

DLG Test Report 7230

IBV Hungária Lighting and Plastic Processing Kft

771-Farmer

Resistance to ammonia,
cleaning distance



IBV HUNGÁRIA
771-FARMER
✓ Resistance to ammonia
✓ Cleaning distance
DLG Test Report 7230



Overview

A test mark “DLG-APPROVED for individual criteria” is awarded for agricultural products which have successfully fulfilled a scope-reduced usability testing conducted by DLG according to independent and recognized evaluation criteria. The test is intended to highlight particular innovations and key criteria of the test object. The test may contain criteria from the DLG test scope for overall tests, or focus on other value-determining characteristics and properties of the test subject. The minimum requirements, test conditions and procedures as well as the evaluation bases of the test results will be specified in consultation with an expert group of DLG. They correspond to the recognized rules of technology, as well as scientific and agricultural knowledge and requirements. The successful testing is concluded with the publication of a test report, as well as the awarding of the test mark which is valid for five years from the date of awarding.



**IBV HUNGÁRIA
771-FARMER**
 ✓ Resistance to ammonia
 ✓ Cleaning distance
 DLG Test Report 7230

The ammonia resistance test was performed as a laboratory test according to the patented DLG test standard. This test is intended to determine the suitability of equipment for animal living areas to withstand the impacts of animal environments. The cleaning distance test assesses the suitability for cleaning animal living areas.

Other criteria were not tested.

Assessment in brief

The LED Light “771-Farmer” from IBV Hungária has successfully completed the DLG test for ammonia resistance and cleaning distance. According to this result,

it can be assumed that these luminaires are resistant to the typical environmental conditions of animal living areas and that no accelerated reduction of the

product lifetime will occur. In addition, LED Light “Farmer-771” was operated actively in the chamber for the entirety of the test. No product damage was observed here.

Table 1:
Assessment in brief

DLG QUALITY PROFILE	Evaluation*
Ammonia resistance	■ ■ ■ ■ □
Preservation of the luminous flux	■ ■ ■ □ □
Cleaning distance	■ ■ ■ ■ □

Furthermore, the cleaning distance is regarded as suitable for the cleaning of animal houses.

* DLG Evaluation range:
 ■ ■ ■ or better = meets, exceeds or significantly exceeds the established DLG standards
 ■ = meets the legal requirements for marketability, ■ = failed

The Product

Manufacturer and Applicant

IBV Hungária Lighting and Plastic Processing Kft
H-6100 Kiskunfélegyháza
Csanyi út 71
Hungary

Product:
LED Light “771-Farmer”

Contact:
Phone +36 704632100
Fax +36 704632170
info@ibv.hu, sales@ibv.hu
www.ibv.hu

Description and Technical Data

The LED Light “771-Farmer” tested is suitable for use in animal housings, in agricultural farm buildings and for unprotected outdoor use.

Table 2:
Technical data (according to manufacturer)

LED Light 771-Farmer	
Electrical connection	
Voltage	220 - 240V AC
Frequency	50 Hz
Performance	43 W
Dimension and weight	
Length x Width x Height	1,577 mm x 112 mm x 99 mm
Weight	2.2 kg
Additional technical data	
Number of LED modules	1*
Housing material	glass fibre reinforced polyester (GRP)
Cover	Opal Acrylic PMMA
Material of brackets	stainless steel
Protection rating	IP 66
Colour temperature	5,000 K (optional 4,000 K)
Dimmable	no (DALI optional)
Beam angle	120°
Rated luminous flux	6,600 lm
Luminous efficacy	154 lm/W

* Zhaga standard, replaceable, including connector

The Method

Resistance to ammonia

The ammonia resistance of the LED light “771-Farmer” was determined by a laboratory test with one luminaire according to the patented DLG test standard for agricultural use. The laboratory test is designed to replicate the conditions of a usage period of about 10 years exposure to animal living areas.

The test was carried out in a climate chamber under the following climate conditions:

Test duration	1500 h
Air temperature	70 °C
Relative humidity	70 %
Ammonia concentration	750 ppm

For assessing the ammonia resistance, each luminaire was examined visually, gravimetrically and the plastic parts additionally through measurement of the hardness (Shore D) before and after the climate testing. The luminaires have additionally been following a cycle of operation predefined by DLG (3 hours on, 1 hour off) in order to evaluate any thermal impacts caused by switch-on and -off procedures during ammonia fumigation. Furthermore the luminous flux was measured according to DIN EN 13032 before and after the fumigation in order to get additional information regarding the aging process.

In order to avoid overheating (> 70 °C), the luminaires could be operated at a reduced power level during the testing period.

Cleaning distance

During test bench examinations of the mechanical resistance to high-pressure cleaners, the minimum cleaning distance was determined.

The minimum cleaning distance is defined as the distance between nozzle and surface when no damages can be observed at the housing surface.

The test was conducted under the conditions presented in table 3.

Table 3:

Test conditions cleaning distance

Line pressure	~150 bar
Water	cold, approx. 1,000 l/h, no detergents
Nozzle type	Flat spray nozzle, 25°
Exposition time	1 minute
Distance	200 mm, 150 mm, 100 mm, 50 mm
Ambient temperature	10-20 °C

For all test procedures, the LED Light “771-Farmer” in the length of 1,577 mm has been used. After the tests, the luminaires underwent visual examination to a reference sample that was identical in construction.

Die Testergebnisse im Detail

Resistance to ammonia

Visual test

The comparative visual examination after the ammonia exposure has shown minor discolorations outside the luminaire housing, but no negative impact on the luminaire performance needs to be expected. A slight deformation of the case could have been caused by the continuous thermal load.

During the test, the luminaire appeared to be sufficiently gas-tight. Nevertheless it cannot be ruled out, that a limited amount of ammonia respectively ammonium compounds could enter the luminaire housing. This has not been verified. Again, no negative impact on the luminaire performance needs to be expected.

The defects are rated as insignificant. The examination of the manufacturer's mounting parts didn't also show any defects.

Gravimetric test

Weight comparisons before and after the ammonia fumigation have not shown any measurable increases or decreases in weight. All determined changes were within the measurement uncertainty.

Hardness test

During the hardness test (Shore D) no measurable changes were observed. All determined changes were within the measurement uncertainty.

Functional test

No defects were observed. All luminaires worked after the conducted tests.

Preservation of the luminous flux

After completion of the test the luminaire still had a luminous flux of 75.6 %.

Based on the results of these tested parameters, the luminaire is evaluated as resistant to ammonia.

Cleaning distance

Even at a cleaning distance of only 10 cm, no damages to the luminaire could be observed. At no time a water ingress into the luminaires was noticed. In order to avoid damage to the luminaires during cleaning a minimum cleaning distance of 10 cm should always be ensured.

Summary

The results show that the LED Light "771-Farmer" fulfills the testing requirements for ammonia resistance and cleaning distance and thus receives the test mark DLG-Approved. It can be expected that the luminaire is resistant to ammoniacal air in animal living areas and that no accelerated reduction of the product lifetime occurs.

The LED Light "771-Farmer" was operated both passively and actively during the ammonia fumigation in the test chamber and passed both tests successfully.

It is also recommended in any case to keep a minimum distance of 10 cm during cleaning.

More information

Test implementation

DLG TestService GmbH, Gross-Umstadt location

The tests are conducted on behalf of DLG e.V.

DLG test scope

DLG-approved single criteria test

“Ammonia resistance“ (current as of 03/2021)

Department

Agriculture

Head of Department

Dr. Ulrich Rubenschuh

Test engineer(s)

Dipl.-Ing. (FH) Tommy Pfeifer*

Photometric laboratory

Photometrik GmbH, Einsteinstraße 24

64859 Eppertshausen, Germany

* Author

DLG – the open network and professional voice

Founded in 1885 by the German engineer Max Eyth, DLG (Deutsche Landwirtschafts-Gesellschaft – German Agricultural Society) is an expert organisation in the fields of agriculture, agribusiness and the food sector. Its mission is to promote progress through the transfer of knowledge, quality standards and technology. As such, DLG is an open network and acts as the professional voice of the agricultural, agribusiness and food sectors.

As one of the leading organisations in the agricultural and food market, DLG organises international trade fairs and events in the specialist areas of crop production, animal husbandry, machinery and equipment for farming and forestry work as well as energy supply and food technology. DLG's quality tests for food, agricultural equipment and farm inputs are highly acclaimed around the world.

For more than 130 years, our mission has also been to promote dialogue between academia, farmers and

the general public across disciplines and national borders. As an open and independent organisation, our network of experts collaborate with farmers, academics, consultants, policymakers and specialists in administration in the development of future-proof solutions for the challenges facing the agriculture and the food industry.

Leaders in the testing of agricultural equipment and input products

The DLG Test Center Technology and Farm Inputs and its test methods, test profiles and quality seals hold a leading position in testing and certifying equipment and inputs for the agricultural industry. Our test methods and test profiles are developed by an independent and impartial commission to simulate in-field applications of the products. All tests are carried out using state-of-the-art measuring and test methods applying also international standards.

Internal test code DLG: 2112-0032

Copyright DLG: © 2022 DLG



DLG TestService GmbH
Groß-Umstadt location

Max-Eyth-Weg 1 • 64823 Groß-Umstadt • Germany

Phone: +49 69 24788-600 • Fax: +49 69 24788-690

Tech@DLG.org • www.DLG.org

Download of all
DLG test reports free of charge
at: www.DLG-Test.de