


DOTLUX GmbH

# HIGHFORCE

Resistance to ammonia,  
cleaning distance



**DOTLUX  
HIGHFORCE**

- ✓ Resistance to ammonia
- ✓ Cleaning distance

DLG Test Report 7539

## Overview

A test mark “DLG APPROVED for individual criteria“ is awarded for agricultural products which have successfully fulfilled a scope-reduced usability testing conducted by DLG according to independent and recognized evaluation criteria. The test is intended to highlight particular innovations and key criteria of the test object. The test may contain criteria from the DLG test scope for overall tests, or focus on other value-determining characteristics and properties of the test subject. The minimum requirements, test conditions and procedures as well as the evaluation bases of the test results will be specified in consultation with an expert group of DLG. They correspond to the recognized rules of technology, as well as scientific and agricultural knowledge and requirements. The successful testing is concluded with the publication of a test report, as well as the awarding of the test mark which is valid for five years from the date of awarding.



**DOTLUX  
HIGHFORCE**  
✓ Resistance to ammonia  
✓ Cleaning distance  
DLG Test Report 7539

The ammonia resistance test was performed as a laboratory test according to the patented DLG test standard. This test is intended to determine the suitability of equipment for animal living areas to withstand the impacts of animal environments. The cleaning distance test assesses the suitability for cleaning animal living areas.

Other criteria were not tested.

## Assessment – Brief Summary

The LED light “HIGHFORCE” from company DOTLUX GmbH has successfully completed the DLG test for ammonia resistance and cleaning distance.

According to this result, it can be assumed that these luminaires are resistant to the typical environmental conditions of animal living areas and that no accelerated reduction of the product lifetime will occur.

In addition, the luminaire was operated actively in the chamber for the entirety of the test. No product damage was observed here.

Furthermore, the tested cleaning distance is suitable for use in practical farms.

*Table 1:  
Overview of results*

DLG QUALITY PROFIL	Evaluation*
Resistance to ammonia	■ ■ ■ ■ □
Preservation of luminous flux	■ ■ ■ ■ □
Cleaning distance	■ ■ ■ ■ □

\* DLG Evaluation range:

■ ■ ■ or better = meets, exceeds or significantly exceeds the established DLG standards,  
■ ■ = meets the legal requirements for marketability, ■ = failed

## The Product

### Manufacturer and applicant

DOTLUX GmbH  
Richard-Stücklen-Straße 7  
91781 Weißenburg  
Deutschland

Product:

LED light "HIGHFORCEabs, HIGHFORCEnarrow, HIGHFORCEwide"

Contact:

Phone +49 (0)9141 4051-202  
Telefax +49 (0)9141 4051-999  
info@dotlux.de  
www.dotlux.de

### Description and technical data

The tested LED light "HIGHFORCE" is suitable for any usage in animal housing surroundings.

Table 2:

Technical data (according to manufacturer)

	HIGHFORCEabs, HIGHFORCEnarrow, HIGHFORCEwide	
	1,175 mm	1,455 mm
<b>Electrical connection</b>		
Voltage	230 V	
Frequency	50-60 Hz	
Performance	18/22/30/43 W	22/27/37/54 W
<b>Dimension and weight</b>		
Length	1,175 mm	1,455 mm
Width	90 mm	
Height	93 mm	
Weight	1.5 kg	1.8 kg
<b>Additional technical data</b>		
Number of LED modules	1/2/3	
Housing material	diffuser: translucent AC, body: dark grey ABS	
Colour temperature	3,000/4,000/5,000/6,500 K	
Dimmable	no, Dali (optional)	
Light angle	lambertian/narrow/wide beam	
Rated luminous flux	2,340... 7,170 lm	

## The Method

### Resistance to ammonia

The ammonia resistance of the LED light “HIGHFORCE” was determined by a laboratory test with four single luminaires according to the patented DLG test standard for agricultural use. The laboratory test is designed to replicate the conditions of a usage period of about 10 years exposure to animal living areas.

The test was carried out in a climate chamber under the following climate conditions:

Test duration	1500 h
Air temperature	70 °C
Relative humidity	70 %
Ammonia concentration	750 ppm

For assessing the ammonia resistance, each luminaire was examined visually, gravimetrically and the plastic parts additionally through measurement of the hardness (Shore D) before and after the climate testing. The luminaires have additionally been following a cycle of operation predefined by DLG (3 hours on, 1 hour off) in order to evaluate any thermal impacts caused by switch-on and -off procedures during ammonia fumigation.

In order to avoid overheating ( $> 70\text{ °C}$ ), the luminaires could be operated at a reduced power level during the testing period.

### Cleaning distance

During test bench examinations of the mechanical resistance to high-pressure cleaners, the minimum cleaning distance was determined.

The minimum cleaning distance is defined as the distance between nozzle and surface when no damages can be observed at the housing surface.

The test was conducted under the conditions presented in table 3.

Table 3:

#### Test conditions cleaning distance

Line pressure	~150 bar
Water	cold, approx. 1,000 l/h, no detergents
Nozzle type	Flat spray nozzle, 25°
Exposition time	1 minute
Distance	200 mm, 150 mm, 100 mm, 50 mm
Ambient temperature	10 ... 20 °C

For the approval of all luminaires in table 2, the LED light “HIGHFORCE” in length of 1,455 mm has been used. After the tests, the luminaires underwent visual examination to a reference sample that was identical in construction.

## The Test Results in Detail

### Resistance to ammonia

#### *Visual test*

The comparative visual examination after the ammonia exposure has shown minor discolorations at the luminaire housing.

During the test, the tube light appeared to be sufficiently gas-tight. Nevertheless it cannot be ruled out, that a limited amount of ammonium compounds could enter the luminaire housing. Again, no negative impact on the luminaire performance needs to be expected.

The defects are rated as insignificant. The examination of the manufacturer's mounting parts didn't also show any defects.

#### *Gravimetric test*

Weight comparisons before and after the ammonia fumigation have not shown any measurable increases or decreases in weight.

#### *Hardness test*

During the hardness test (Shore D) no measurable changes were observed. All determined changes were within the measurement uncertainty.

#### *Functional test*

No defects were observed. All luminaires worked after the conducted tests.

#### *Preservation of the luminous flux*

After completion of the test the luminaire still had a luminous flux of 87.5 %.

Based on the results of these tested parameters, the luminaire is evaluated as resistant to ammonia.

### Cleaning distance

Even at a cleaning distance of only 10 cm, no damages to the luminaire could be observed.

At no time a water ingress into the luminaires was noticed.

In order to avoid damage to the luminaires during cleaning reliably, according to the manufacturer's specifications a minimum cleaning distance of 10 cm should always be ensured.

## Summary

The results show that the LED light "HIGHFORCE" fulfills the testing requirements for ammonia resistance and cleaning distance and thus receives the test mark DLG-Approved. It can be expected that the luminaire is resistant to ammoniacal air in animal living areas and that no accelerated reduction of the product lifetime occurs.

The LED light "HIGHFORCE" was operated both passively and actively during the ammonia fumigation in the test chamber and passed both tests successfully.

It is also recommended in any case to keep a minimum distance of 10 cm during cleaning.

## Further information

### Testing agency

DLG TestService GmbH,  
Gross-Umstadt location, Germany  
The tests are conducted on behalf of DLG e.V.

### DLG test framework

DLG-APPROVED Test “Ammonia resistance”  
(current as of 03/2021)

### Department

Farm inputs

### Division head

Dr. Michael Eise

### Test engineer(s)

Dipl-Ing (FH) Tommy Pfeifer\*

### Photometric laboratory

Photometrik GmbH, Einsteinstraße 24,  
64859 Eppertshausen, Germany

\* Author

## DLG. An open network and professional voice.

Founded in 1885 by the German engineer Max Eyth, DLG (Deutsche Landwirtschafts-Gesellschaft – German Agricultural Society) is an expert organisation in the fields of agriculture, agribusiness and the food sector. Its mission is to promote progress through the transfer of knowledge, quality standards and technology. As such, DLG is an open network and acts as the professional voice of the agricultural, agribusiness and food sectors.

As one of the leading organisations in the agricultural and food market, DLG organises international trade fairs and events in the specialist areas of crop production, animal husbandry, machinery and equipment for farming and forestry work as well as energy supply and food technology. DLG's quality tests for food, agricultural equipment and farm inputs are highly acclaimed around the world.

For more than 130 years, our mission has also been to promote dialogue between academia, farmers and

the general public across disciplines and national borders. As an open and independent organisation, our network of experts collaborate with farmers, academics, consultants, policymakers and specialists in administration in the development of future-proof solutions for the challenges facing the agriculture and the food industry.

### Leaders in the testing of agricultural equipment and input products

The DLG Test Center Technology and Farm Inputs and its test methods, test profiles and quality seals hold a leading position in testing and certifying equipment and inputs for the agricultural industry. Our test methods and test profiles are developed by an independent and impartial commission to simulate in-field applications of the products. All tests are carried out using state-of-the-art measuring and test methods applying also international standards.

The HIGHFORCE was tested for the first time in 2019 and in the same year the test results were published in the DLG test report 7021. Re-certification was applied for in 2025. Due to a change in the DLG test framework, the luminaire was subjected to a re-measurement and passed again. According to the manufacturer, the HIGHFORCE will be sold unchanged in the originally tested version.

Internal test code DLG: 2502-0035

Copyright DLG: © 2025 DLG



**DLG TestService GmbH**

**Groß-Umstadt location**

Max-Eyth-Weg 1 • 64823 Groß-Umstadt • Germany

Phone +49 69 24788-600 • Fax +49 69 24788-690

Tech@DLG.org • www.DLG.org

**Download of all  
DLG test reports free of charge  
at: [www.DLG-Test.de](http://www.DLG-Test.de)**